

Stepper Motor System with Medium Torque Drive

Tests performed:

- 1. Torque versus Regulated Current
- 2. Maximum RPM
- 3. Thermal Imaging
- 4. Current waveforms using 12V, 700mA, 100 RPM
 - a. Full step, fast decay with synchronous rectification
 - b. Full step, fast decay without synchronous rectification
 - c. Full step, mixed decay (DECAY = 1V)
 - d. Full step, mixed decay (DECAY = 1.3V)
 - e. Full step, slow decay
 - f. 1/2 microstep, fast decay with synchronous rectification
 - g. 1/2 microstep, fast decay without synchronous rectification
 - h. 1/2 microstep, mixed decay (DECAY = 1V)
 - i. 1/2 microstep, mixed decay (DECAY = 1.3V)
 - j. 1/2 microstep, slow decay
 - k. 1/4 microstep, fast decay with synchronous rectification
 - I. 1/4 microstep, fast decay without synchronous rectification
 - m. 1/4 microstep, mixed decay (DECAY = 1V)
 - n. 1/4 microstep, mixed decay (DECAY = 1.3V)
 - o. 1/4 microstep, slow decay
 - p. 1/8 microstep, fast decay with synchronous rectification
 - g. 1/8 microstep, fast decay without synchronous rectification
 - r. 1/8 microstep, mixed decay (DECAY = 1V)
 - s. 1/8 microstep, mixed decay (DECAY = 1.3V)
 - t. 1/8 microstep, slow decay
- 5. Current ramp rate versus VM
 - a. VM = 8V
 - b. VM = 12V
 - c. VM = 20V
- 6. Current regulation (zoomed-in)
 - a. Fast decay with synchronous rectification, $t_{OFF} = 20 \mu s$
 - b. Fast decay with synchronous rectification, $t_{OFF} = 47 \mu s$
 - c. Fast decay without synchronous rectification, $t_{OFF} = 47 \mu s$
 - d. Mixed decay (DECAY = 1V), $t_{OFF} = 47 \mu s$
 - e. Mixed decay (DECAY = 1.3V), $t_{OFF} = 47 \mu s$
 - f. Slow decay, $t_{OFF} = 47 \mu s$
 - g. $t_{BLANK} = 1.4 \mu s$, Fast decay
 - h. $t_{BLANK} = 1.4\mu s$, Mixed decay (DECAY = 1V)
 - i. $t_{BLANK} = 1.4 \mu s$, Mixed decay (DECAY = 1.7V)
 - j. $t_{BLANK} = 7\mu s$, Fast decay
 - k. $t_{BLANK} = 7\mu s$, Mixed decay (DECAY = 1V)
 - I. $t_{BLANK} = 7\mu s$, Mixed decay (DECAY = 1.7V)




Recommended baseline settings:

1/8 microstep, synchronous rectification enabled, mixed decay with DECAY = 1V, $I_{CHOP} = 700$ mA, $t_{OFF} = 47$ µs, $t_{BLANK} = 1.4$ µs, STEP frequency = 2.7kHz.

Section 1: Torque versus Regulated Current

Data was collected at 60 RPM, 1/2 microstep, using a magnetic particle brake load. Loading was increased until rotor stall. These torque values are approximations.

I _{CHOP}	Torque	
0.5A	29 oz-in	205 mNm
1A	68 oz-in	480 mNm
1.5A	100 oz-in	703 mNm
2A	124 oz-in	876 mNm
2.5A	141 oz-in	994 mNm






Section 2: Maximum RPM

Using VM = 12V, 1/8 microstepping, and $I_{CHOP} = 0.92A$:




Section 3: Thermal Imaging

Data was collected with VM = 12V, I_{CHOP} = 2.5A.






Section 4: Current waveforms using 12V, 700mA, 100 RPM




Full step, fast decay with synchronous rectification






Full step, fast decay without synchronous rectification




Full step, mixed decay (DECAY = 1V)






Full step, mixed decay (DECAY = 1.3V)




Full step, slow decay






1/2 microstep, fast decay with synchronous rectification




1/2 microstep, fast decay without synchronous rectification






1/2 microstep, mixed decay (DECAY = 1V)




1/2 microstep, mixed decay (DECAY = 1.3V)






1/2 microstep, slow decay




1/4 microstep, fast decay with synchronous rectification






1/4 microstep, fast decay without synchronous rectification




1/4 microstep, mixed decay (DECAY = 1V)






1/4 microstep, mixed decay (DECAY = 1.3V)




1/4 microstep, slow decay






1/8 microstep, fast decay with synchronous rectification




1/8 microstep, fast decay without synchronous rectification






1/8 microstep, mixed decay (DECAY = 1V)



1/8 microstep, mixed decay (DECAY = 1.3V)






1/8 microstep, slow decay




Section 5: Current ramp rate versus VM




VM = 8V






VM = 12V



VM = 20V




Section 6: Current regulation (zoomed-in)




Fast decay with synchronous rectification, $t_{OFF} = 20 \mu s$






Fast decay with synchronous rectification, $t_{\text{OFF}} = 47 \mu s$




Fast decay without synchronous rectification, $t_{OFF} = 47\mu s$






Mixed decay (DECAY = 1V), $t_{OFF} = 47 \mu s$




Mixed decay (DECAY = 1.3V), $t_{OFF} = 47\mu s$






Slow decay, $t_{OFF} = 47 \mu s$




 $t_{BLANK} = 1.4\mu s$, Fast decay






 $t_{BLANK} = 1.4\mu s$, Mixed decay (DECAY = 1V)




 $t_{BLANK} = 1.4\mu s$, Mixed decay (DECAY = 1.7V)






 $t_{BLANK} = 7\mu s$, Fast decay



 $t_{BLANK} = 7\mu s$, Mixed decay (DECAY = 1V)





 $t_{BLANK} = 7\mu s$, Mixed decay (DECAY = 1.7V)

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated