设计指南: TIDM-02007

在单个 MCU 上使用快速电流环路 (FCL) 和 SFRA 的双轴电机驱动器参考设计

TEXAS INSTRUMENTS

说明

此参考设计提供了一种在单个 C2000TM控制器上使用快速电流环路 (FCL) 和软件频率响应分析器 (SFRA) 技术的双轴电机驱动器。FCL 可利用 CPU 和 CLA 并行处理技术来显著改善控制带宽和相位裕度,降低反馈采样和PWM 更新之间的延迟,实现更高的控制带宽和最大调制指数,提高驱动器的直流总线利用率和电机的转速范围。开发人员可通过集成的 SFRA 工具快速测量应用的频率响应,以调整转速和电流控制器。鉴于 C2000 系列 MCU 的系统级集成和高性能,它能够同时支持双轴电机驱动器要求,以更高的性能提供非常强大的位置控制。该软件在 C2000WARE MotorControl SDK 中发布。

资源

| TIDM-02007 | 设计文件夹 |
|----------------------------|-------|
| LAUNCHXL-F28379D | 工具文件夹 |
| LAUNCHXL-F280049C | 工具文件夹 |
| BOOSTXL-3PHGANINV | 工具文件夹 |
| C2000WARE-MOTORCONTROL-SDK | 工具文件夹 |



Search Our E2E™ support forums


特性

- 三相 GaN 逆变器具有 12V 到 60V 的宽输入电压范围,每个相位的均方根电流和峰值输出电流分别为7A 和 10A
- 精密相电流感应具有高精度 (0.1%),基于直列式分流电阻器 BoosterPackTM
- 使用现有的硬件套件在单个 F2837x 或 F28004x MCU 上实现具有快速电流环路 (FCL) 的双轴电机驱动器
- 工作软件与 F2837x 或 F28004x 兼容,可作为具有专门知识或有限专业知识的人士的起点
- 使用 FCL 技术同时实现外部位置和速度环路以及内部扭矩环路,以在每个电机上实现快速响应
- 集成的 SFRA 工具支持对转速和电流环路单独进行 在线调优
- 增量系统构建旨在验证系统中使用的主要软件模块
- 较低的 PWM 更新延迟(F2837x 为 1.02μs, F28004x 为 2.02μs)可实现更高的控制带 宽和调制指数

应用

- 伺服驱动器电源模块
- 伺服驱动器功率级模块
- 扫地机器人







该 TI 参考设计末尾的重要声明表述了授权使用、知识产权问题和其他重要的免责声明和信息。



System Description www.ti.com.cn

1 System Description

High-performance motor drives in servo drive and robotics applications are expected to provide high precision and high control bandwidth of current, speed, and position loops for superior control of end applications such as robotics, CNC machines, and so forth. Since the current loop makes up the inner most control loop, it must have a high bandwidth to enable the outer speed or position loops to be faster. Hence, a high bandwidth Fast Current Loop (FCL) is needed in high performance industrial servo control applications. However, the delays due to ADC conversion and algorithm execution limit the current controller bandwidth to about a tenth of the sampling frequency.

This reference design shows the implementation of fast current loop on a F2837x/F28004x C2000 controller running two motors simultaneously, and verifies the frequency response of the control loops using Tl's SFRA tool. The control bandwidth of fast current loop and the operating speed range of motor are experimentally verified. This design guide documents the test platform setup, procedure and the quantitative results obtained. It is important to note that when the PWM carrier frequency is 10 KHz, the current loop bandwidth obtained is 5 KHz for a phase margin of 45° over a wide speed range compared to the traditional MCU based systems, FCL software can potentially triple a drive system's torque response and double its maximum speed without increasing the PWM carrier frequency.

The F2837x and F28004x series of C2000 MCU enable a new value point for dual-axis drives that also delivers very robust motion-control performance. The value comes not only from the achievable control performance and ability to drive two motors concurrently, but also from the high degree of on-chip integration of other key electronic system functions. Since both F2837x and F28004x devices support CPU and CLA cores, CPU offload encoder feedback and torque control processing to the CLA to maximize the performance of dual-axis servo drive.

1.1 Key System Specifications

表 1. Key System Specifications

| PARAMETER | SPECIFICATIONS | |
|--|--|--|
| DC Input Voltage | 24 V (12 to 60 V, 80 V absolute max) | |
| Maximum three-phase output current | 7 A _{RMS} , 10 A (peak) per phase | |
| Maximum sampling current | ±16.5 A (1.65-V offset bias, 3.3-V scaled range) | |
| Maximum input power | 200 W (at 24 V, each motor every BoosterPack) | |
| Working Temperature range | Ambient temperature: -40°C to 85°C | |
| Switching PWM Frequency | 10 to 30 kHz (single sampling) / 15 kHz (double sampling) on F28004x 10 to 40 kHz (single sampling) / 20 kHz (double sampling) on F2837x | |
| Running frequency range | 0~400 Hz at the M-2310P motor | |
| Maximum efficiency at 10-kHz PWM frequency | 90% at rate power of the M-2310P motor | |
| Maximum Modulation Index at 10-kHz PWM frequency | 96% (single sampling), 92% (double sampling) on F28004x 98% (single sampling), 96% (double sampling) on F2837x | |
| PWM Update Latency | 2.02 µs (F28004x) per motor 1.02 µs (F2837x) per motor | |
| Overtemperature Software/Hardware Protection Overcurrent protection Undervoltage and overvoltage protection | | |



www.ti.com.cn System Overview

2 System Overview

2.1 Block Diagram

■ 1 illustrates the dual-axis motor drive based a single C2000 MCU system block diagram of the TIDM-02007 reference design, which includes the following elements:

- One controller board, a TMS320F28379D LaunchPad™ or TMS320F280049C LaunchPad
 - Higher clock frequency CPU, Trigonometric Math Unit (TMU) and control law accelerator (CLA) that
 parallel process floating point calculation of FOC and FCL algorithm to get high speed, precision
 performance.
 - Four high-speed precision 12-bit and 16-bit ADCs on F2837x, or three high speed precision 12-bit
 ADCs on F28004x for sensing the motor phase current and DC bus voltage.
 - Two independent Enhanced Quadrature Encoder Pulse (QEP)-based encoder connectors for sensing the exact rotor position for dual-axis motor drive.
 - On-board USB can work as both a debugger for debugging and programming interface and a virtual COM port to a PC with a serial monitor running for SFRA software.
- Two Inverter boards, BOOSTXL-3PHGANINV
 - Wide Input Voltage Range 12-V to 60-V with 7-ARMS Output Current per Phase.
 - Precision in-line phase current sensing with 5-mΩ shunt for motor drive that can be connected to the ADC of F28379D or F280049C.
 - Three LMG5200 GaN half-bridge power stages with embedded driver that are compatible interface
 With 3.3-V I/O for F28379D or F280049C LaunchPad.

SCIA PWM-1 A B RX 1B CPU (FPU, TMU) A B 2Δ PWM-2 la1(option 32 bit 2B В EQEP1 1B 2A 2B 2A PWM-3 lb1 Gate 3B М1 Driver BL CLA OC1 lc1 В **FQFP**2 4Α -1 A B PWM-4 Incremental 4B Encoder CLB CANA 5A PWM-5 5B Vdc1 BoostXL-3PhGanInv 6A PWM-6 DMA OC2 A1 CMP1 la1 ADCA 12/16 bit A2 CMP2 la2 4A 4B 5A 5B 6A lb1 ADCB lb2 12/16 bit B2 Gate ВН CMP4 lb2 ≶ М2 Driver C1 CMP5 lc1 lc2 ADCC 6B

CMP6

lc2

Vdc1

Vdc2

12/16 bit C2

12/16 bit D2

ADCD

F2837x / F28004x LaunchPad

图 1. TIDM-02007 Dual-Axis Motor Drive System Block Diagram

Vdc2

Incrementa

Encoder

BoostXL-3PhGanInv



System Overview www.ti.com.cn

2.2 Design Considerations

The major challenge in implementing the current loop lies in reducing the latency between feedback sampling and PWM updates. In traditional control schemes, this latency is typically one sampling period, thereby, delaying the control action. For a fast current loop, this delay must be as small as possible to improve the loop performance over the wide operating speed range of the motor. Typically, a latency of one microsecond or less is considered acceptable in many applications that requires a controller with a fast compute engine, a fast ADC, low latency control peripherals and a superior control algorithm on a single F2837x or F28004x, it is possible to run two independent FCLs in less than 1 μs on F2837x or 2 μs on F28004x separately while still supporting the high control bandwidth and double sampling of each axis. In order to maintain the goal of measuring the currents of each motor during voltage transitions, the ADC double sampling is interleaved between each motor so that the sampling and subsequent FOC processing does not need to happen back to back. The motor 1 carrier lags motor 2 by a fixed 90°, then the ADC sampling period is consistent across both motors but interleaved between them as shown in 🗵 2. Each ADC sample and conversion is followed by the C2000 CPU performing the FOC algorithm and updating the PWMs. In this way, the sample-to-PWM update remains very consistent for each execution, whether it's the first or second sample of motor 1 or motor 2.




图 2. Motor Phase Current Sampling and PWM Output Update for Dual-Axis Motor Drive

2.3 Highlighted Products

2.3.1 TMS320F28004x

TMS320F28004x is a powerful 32-bit floating-point microcontroller unit (MCU) that lets designers incorporate crucial control peripherals, differentiated analog, and nonvolatile memory on a single device. The real-time control subsystem is based on Ti's 32-bit C28x CPU, which provides 100 MHz of signal processing performance. The C28x CPU is further boosted by the new TMU extended instruction set, which enables fast execution of algorithms with trigonometric operations commonly found in transforms and torque loop calculations. The CLA allows significant offloading of common tasks from the main C28x CPU. The CLA is an independent 32-bit floating-point math accelerator that executes in parallel with the



www.ti.com.cn System Overview

CPU. Additionally, the CLA has its own dedicated memory resources and it can directly access the key peripherals that are required in a typical control system. High-performance analog blocks are integrated on the F28004x MCU to further enable system consolidation. Three separate 12-bit ADCs provide precise and efficient management of multiple analog signals, which ultimately boosts system throughput. Seven PGAs on the analog front end enable on-chip voltage scaling before conversion. Seven analog comparator modules provide continuous monitoring of input voltage levels for trip conditions. The TMS320C2000™ devices contain industry-leading control peripherals with frequency-independent ePWM/HRPWM and eCAP allow for a best-in-class level of control to the system. A specially enabled device variant, TMS320F28004xC, allows access to the Configurable Logic Block (CLB) for additional interfacing features.

2.3.2 TMS320F2837x

TMS320F2837xD is a powerful 32-bit floating-point microcontroller unit (MCU) designed for advanced closed-loop control applications such as industrial motor drives; solar inverters and digital power; electrical vehicles and transportation; and sensing and signal processing. The dual real-time control subsystems are based on TI's 32-bit C28x floating-point CPUs, which provide 200 MHz of signal processing performance in each core. The C28x CPUs are further boosted by the new TMU accelerator, which enables fast execution of algorithms with trigonometric operations common in transforms and torque loop calculations. The F2837xD microcontroller family features two CLA real-time control coprocessors. The CLA is an independent 32-bit floating-point processor that runs at the same speed as the main CPU. The CLA responds to peripheral triggers and executes code concurrently with the main C28x CPU. This parallel processing capability can effectively double the computational performance of a real-time control system. By using the CLA to service time-critical functions, the main C28x CPU is free to perform other tasks, such as communications and diagnostics. The dual C28x+CLA architecture enables intelligent partitioning between various system tasks. For example, one C28x+CLA core can be used to track speed and position, while the other C28x+CLA core can be used to control torque and current loop. Performance analog and control peripherals are also integrated on the F2837xD MCU to further enable system consolidation. Four independent 16-bit ADCs provide precise and efficient management of multiple analog signals, which ultimately boosts system throughput. The Comparator Subsystem (CMPSS) with windowed comparators allows for protection of power stages when current limit conditions are exceeded or not met. Other analog and control peripherals include DACs, PWMs, eCAPs, eQEPs, SDFMs, and other peripherals.

2.3.3 LMG5200

The LMG5200 device, an 80-V, 10-A driver plus GaN half-bridge power stage provides an integrated power stage solution using enhancement-mode Gallium Nitride (GaN) FETs. The device consists of two GaN FETs driven by one high-frequency GaN FET driver in a half-bridge configuration. GaN FETs provide significant advantages for power conversion as they have near-zero reverse recovery and very-small input capacitance C_{ISS} . The LMG5200 is mounted on a completely bond-wire-free package platform with minimized package parasitic elements. The LMG5200 device is available in a 6- \times 8- \times 2-mm lead free package and can be easily mounted on PCBs. The LMG5200 reduces the board requirements for maintaining clearance requirements for medium-voltage GaN applications while minimizing the loop inductance to ensure fast switching. The LMG5200 is specified over the extended operating temperature range (-40° C to 125°C)



System Overview www.ti.com.cn

2.3.4 INA240

The INA240 is a voltage-output, current sense amplifier with enhanced PWM rejection that can sense drops across shunt resistors over a wide common-mode voltage range from –4 to 80 V, independent of the supply voltage. Enhanced PWM rejection provides high levels of suppression for large common-mode transients (ΔV/Δt) in systems that use pulse-width modulation (PWM) signals such as three-phase inverters in motor drives. This feature allows for accurate current measurements without large transients and associated recovery ripple on the output voltage. This device operates from a single 2.7- to 5.5-V power supply, drawing a maximum of 2.4-mA of supply current. Four fixed gains are available: 20 V/V, 50 V/V, 100 V/V, and 200 V/V. The low offset of the zero drift architecture enables current sensing with maximum drops across the shunt as low as 10-mV full scale. All versions are specified over the extended operating temperature range (–40°C to 125°C), and are offered in an 8-pin TSSOP package.




www.ti.com.cn System Overview

2.4 System Design Theory

2.4.1 FOC and Position Loop in Servo Drives

图 3 shows the basic position control block diagram of a field oriented control (FOC) based AC motor drive system used in servo drives. The current loop is highlighted here because this is the inner most loop that has a higher influence on the bandwidth of the outer speed and position loops. For the outer position and speed loops to have a higher bandwidth, the inner loop must have a far higher bandwidth, typically more than three times. In the current loop, any two of the motor phase currents are measured, while the third can be estimated from these two sensing currents. These measurements feed the Clarke transformation module. The outputs of this projection are designated I_n and I_B. These two components of the current along with the rotor flux position are the inputs of the Park transformation, which transform them to currents (I_d and I_g) in D-Q rotating reference frame. The I_d and I_g components are compared to the references I_dref (the flux reference) and I_dref (the torque reference). In the synchronous permanent magnet motor, the rotor flux is fixed as determined by the magnets. When controlling a PMSM motor, I_dref can be set to zero, except during field weakening. The torque command I_oref can be from the output of the speed regulator. The outputs of the current regulators are V_dref and V_dref. These outputs are applied to the inverse Park transformation. Using the position of rotor flux, this projection generates V_aref and V_βref, which are the components of the stator vector voltage in the stationary orthogonal reference frame. These components are the inputs of the PWM generation block. The outputs of this block are the signals that drive the inverter. Both Park and inverse Park transformations need the rotor flux position that is obtained from the position encoder in this reference design using sensored-FOC.

图 3. Basic Position Control With Sensored-FOC for a PMSM





System Overview www.ti.com.cn

2.4.2 Fast Current Loop

A minimal current loop time not only helps to improve the control bandwidth, but it also enables a higher modulation index (M-I) for the inverter. A higher M-I translates into the higher phase voltage that the inverter can apply on the motor. Higher loop latency will reduce the maximum available voltage and can restrict the rate of current change in the motor, thereby, adversely impacting the controller performance. To overcome these challenges, a controller with high computational power, right set of control peripherals and superior control algorithm are needed. The TMS320F2837x and TMS20F28004x provide the necessary hardware support for higher performance, and the FCL algorithm from TI that runs on the C2000 MCU provides the needed algorithmic support.

№ 4 shows the block diagram of FCL algorithm with its inputs and outputs. The FCL partitions its algorithm across the CPU, CLA and TMU to bring down the latency to under 1.0 μs on F2837x compared to the acceptable 2.0 μs. The FCL algorithm supports two types of current regulators, a typical PI controller and a complex controller. The complex controller can provide additional bandwidth over the typical PI controller at higher speeds. Both current regulators are provided for user evaluation. For more information on the FCL algorithm, see the *Dual-Axis Motor Control Using FCL and SFRA On a Single C2000™ MCU Application Report*, and the source codes of FCL algorithm is available from the MotorControl SDK software.




图 4. Fast Current Loop Block Diagram



3 Hardware, Software, Testing Requirements, and Test Results

3.1 Required Hardware and Software


The reference design is based on the existing hardware tools, most of which are available from the TI Store. The details of the evaluation hardware and references to the user's guide are listed below:

- CPU Either one LAUNCHXL-F28379D or one LAUNCHXLF280049C.
 - LAUNCHXL-F28379D one unit LAUNCHXL-F28379D Overview User's Guide
 - LAUNCHXLF280049C one unit C2000™ Piccolo™ F28004x Series LaunchPad™ Development Kit
- Inverter (INV) BOOSTXL-3PhGaNInv two units BOOSTXL-3PhGaNInv Evaluation Module User's Guide.
- Motor Dyno Set 2MTR-DYNO one unit (two motors)
- A variable DC power supply rated at 48 V/5 A.

3.1.1 LAUNCHXL-F28379D

₹ 5 shows the layout of LAUNCHXL-F28379D, on-board switches setting as marked. For further details, see the LAUNCHXL-F28379D Overview User's Guide.


图 5. Layout of LAUNCHXL-F28379D and Switches Setting





3.1.2 LAUNCHXL-F280049C

图 6. Layout of LAUNCHXL-F280049C and Switches Setting






3.1.3 BOOSTXL-3PhGaNInv

₹ 7 shows the layout of BOOSTXL-3PhGaNInv, on-board switches setting as marked. For more details, see the BOOSTXL-3PhGaNInv Evaluation Module User's Guide.





3.1.4 Software

The firmware of this design is available in the C2000Ware MotorControl SDK and the detailed description and operation of the firmware are introduced in the Dual-Axis Motor Control Using FCL and SFRA On a Single C2000™ MCU Application Report. 图 8 shows the general structure of the project, The firmware of F2837x and F28004x uses the same project structure, and shares most files for motor drive. The software is built such that two different motors can be controlled independently. The firmware of this reference design is gradually built up in order for the final system can be confidently operated. Six phases of the incremental system build are designed to verify the major software modules used in the system. 表 2 and 表 3 summarize the core functions integrated and tested at each build level in the incremental build approach.



图 8. Project Structure






表 2. Functions Verified in Each Incremental System Build

| BUILD LEVEL | FUNCTIONAL INTEGRATION |
|-------------|---|
| Level 1 | Basic PWM generation |
| Level 2 | Open loop control of motor and calibration of current sensing feedbacks |
| Level 3 | CURRENT MODE - Closing current loop using FCL algorithm |
| Level 4 | SPEED MODE - Closing speed loop using inner FCL verified in LEVEL 3 |
| Level 5 | POSITION MODE - Closing position loop using inner speed loop verified in LEVEL 4 |
| Level 6 | SFRA ANALYSIS - Performing SFRA on current loop running motor in speed mode (LEVEL 4) |

表 3. Functional Modules Used in Each Incremental System Build

| SOFTWARE MODULE | LEVEL 1 | LEVEL 2 | LEVEL 3 | LEVEL 4 | LEVEL 5 | LEVEL 6 |
|-------------------------------|--------------------|------------------------|----------------|----------------------|------------|------------|
| PWM Generation | √√ | √ | √ | √ | √ | √ |
| QEP Interface in CLA | | √√ | √ | √ | √ | √ |
| FOC Functions | | | V V | √ | √ | √ |
| FCL | | | V V | √ | √ | √ |
| Speed Controller | | | | √√ | √ | √ |
| Position Controller | | | | | √√ | |
| SFRA Functions | | | | | | √ √ |
| Note: the symbol √ means this | module is using ar | d the symbol $\sqrt{}$ | means this mod | dule is testing in t | his Level. | |



3.2 Testing and Results

3.2.1 Test Setup

Before mounting the BoosterPacks, ensure that jumpers on both LaunchPad and dual-BoosterPacks are set correctly as shown in 图 5 or 图 6 and 图 7. The motor is a PMSM motor with both QEP and HALL sensors available on its headers J4 and J10, respectively. The control scheme is based on QEP feedback; therefore, its QEP header J4 is fed into the LaunchPad. The BoosterPack suggested for this evaluation will mount directly on to the LAUNCHXLF28379D or LAUNCHXL-F280049C. This connects the analog/digital IOs of the BoosterPack to the appropriate IOs of the CPU. Make sure to match the orientation of inverter BoosterPacks as shown in 图 9 before mounting. Mount one inverter BoosterPack on LaunchPad connectors J1-J4, let us call it inverter INV1. Likewise, mount the other inverter on LaunchPad connectors J5–J8, and call it inverter INV2. Until instructed, leave the INV output headers and QEP headers open. When instructed to connect motor 1, connect motor 1 terminal to INV1 connector terminal as 表 4 and motor's QEP header to QEP-A on LaunchPad. Likewise, when instructed, connect motor 2 to INV2 and its QEP header to QEP-B on LaunchPad.





表 4. Motor Phase Connections to BoosterPack™

| BOOSTXL-3PhGaNInv, J3 CONNECTOR | | M-2310P-LNK-04 MOTOR | | |
|---------------------------------|------|----------------------|-------|--|
| Pin | Name | Pin | Color | |
| 3 | VA | Phase R | Black | |
| 2 | VB | Phase S | Red | |
| 1 | VC | Phase T | White | |



3.2.2 Test Results

The operation and test result at each build level are described in application report Dual-Axis Motor Control Using FCL and SFRA On a Single C2000™ MCU in detail.

10 and 11 show the rotor position, speed and current waveform with controlling dual-axis motor simultaneously.

12 and 13 show the torque current, speed and phase current under 0.6 pu speed by adding or removing a step load.




图 10. Rotor Position and Speed of Dual-Axis Motor








图 12. Speed, Torque Current and Phase Current of One Motor With Adding a Step Load





图 13. Speed, Torque Current and Phase Current of One Motor With Removing a Step Load





www.ti.com.cn Design Files

4 Design Files

This reference design is based on the released C2000 development kits and Evaluation Module, which include LAUNCHXL-F28379D, LAUNCHXL-F280049C, and BOOSTXL-3PHGANINV.

5 Software Files

To download the software files, see the design files at C2000Ware-MOTORCONTROL-SDK.

6 Related Documentation

- 1. Texas Instruments, Fast Current Loop Driverlib Library User's Guide
- 2. Texas Instruments, LAUNCHXL-F28379D Overview User's Guide
- 3. Texas Instruments, C2000™ Piccolo™ F28004x Series LaunchPad™ Development Kit
- 4. Texas Instruments, BOOSTXL-3PhGaNInv Evaluation Module User's Guide
- 5. Texas Instruments, C2000™ Software Frequency Response Analyzer (SFRA) Library and Compensation Designer User's Guide
- 6. Texas Instruments, Dual-Axis Motor Control Using FCL and SFRA On a Single C2000™ MCU Application Report

6.1 商标

C2000, E2E, BoosterPack, LaunchPad, TMS320C2000, Piccolo are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

7 Terminology

- ADC Analog-to-Digital Converter
- **CLA Control Law Accelerator**
- **CMPSS Comparator Subsystem Peripheral**
- **CNC Computer Numerical Control**
- DAC Digital to Analog Converter
- **DMC Digital Motor Control**
- ePWM Enhanced Pulse Width Modulator
- eQEP Enhanced Quadrature Encoder Pulse Module
- FCL Fast Current Loop
- FOC Field-Oriented Control
- **FPGA -** Field Programmable Gate Array
- MCU Microcontroller Unit
- PMSM Permanent Magnet Synchronous Motor
- PWM Pulse Width Modulation
- SFRA Software Frequency Response Analyzer
- TMU Trigonometric Mathematical Unit



About the Author www.ti.com.cn

8 About the Author

YANMING LUO is a Systems Application Engineer in the system solutions team of C2000 at Texas Instruments, where he is responsible for developing reference design solutions for motor drive applications based C2000 controllers. Yanming has been with TI since 2003 and earned an M.S. degree from Northeastern University, China in 1998.

重要声明和免责声明

TI 均以"原样"提供技术性及可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证其中不含任何瑕疵,且不做任何明示或暗示的担保,包括但不限于对适销性、适合某特定用途或不侵犯任何第三方知识产权的暗示担保。

所述资源可供专业开发人员应用TI产品进行设计使用。您将对以下行为独自承担全部责任:(1)针对您的应用选择合适的TI产品;(2)设计、验证并测试您的应用;(3)确保您的应用满足相应标准以及任何其他安全、安保或其他要求。所述资源如有变更,恕不另行通知。TI对您使用所述资源的授权仅限于开发资源所涉及TI产品的相关应用。除此之外不得复制或展示所述资源,也不提供其它TI或任何第三方的知识产权授权许可。如因使用所述资源而产生任何索赔、赔偿、成本、损失及债务等,TI对此概不负责,并且您须赔偿由此对TI及其代表造成的损害。

TI 所提供产品均受TI 的销售条款 (http://www.ti.com.cn/zh-cn/legal/termsofsale.html) 以及ti.com.cn/上或随附TI产品提供的其他可适用条款的约束。TI提供所述资源并不扩展或以其他方式更改TI 针对TI 产品所发布的可适用的担保范围或担保免责声明。

邮寄地址: 上海市浦东新区世纪大道 1568 号中建大厦 32 楼,邮政编码: 200122 Copyright © 2019 德州仪器半导体技术(上海)有限公司

重要声明和免责声明

TI 均以"原样"提供技术性及可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证其中不含任何瑕疵,且不做任何明示或暗示的担保,包括但不限于对适销性、适合某特定用途或不侵犯任何第三方知识产权的暗示担保。

所述资源可供专业开发人员应用TI产品进行设计使用。您将对以下行为独自承担全部责任: (1)针对您的应用选择合适的TI产品; (2)设计、验证并测试您的应用; (3)确保您的应用满足相应标准以及任何其他安全、安保或其他要求。所述资源如有变更,恕不另行通知。TI对您使用所述资源的授权仅限于开发资源所涉及TI产品的相关应用。除此之外不得复制或展示所述资源,也不提供其它TI或任何第三方的知识产权授权许可。如因使用所述资源而产生任何索赔、赔偿、成本、损失及债务等,TI对此概不负责,并且您须赔偿由此对TI及其代表造成的损害。

TI 所提供产品均受TI 的销售条款 (http://www.ti.com.cn/zh-cn/legal/termsofsale.html) 以及ti.com.cn上或随附TI产品提供的其他可适用条款的约束。TI提供所述资源并不扩展或以其他方式更改TI 针对TI 产品所发布的可适用的担保范围或担保免责声明。

邮寄地址: 上海市浦东新区世纪大道 1568 号中建大厦 32 楼,邮政编码: 200122 Copyright © 2019 德州仪器半导体技术(上海)有限公司